**SHORON** 

N CA

# **GENERAL INFORMATION**

# ZAMAC NAILIN®

Nail Anchor

## **PRODUCT DESCRIPTION**

The Zamac Nailin is a nail drive anchor which has a body formed from Zamac alloy. Drive nails are available in carbon or stainless steel. The anchor can be used in concrete, block, brick or stone.

A corrosion resistant Zamac alloy is used to form the anchor body with either a mushroom or flat head. The anchor can be used for light duty, tamperproof applications. The anchor is not recommend for overhead, life-safety or sustained tensile loading applications (see performance data section).

## GENERAL APPLICATIONS AND USES

- Roof Flashing
- Mechanical Attachments
- Brick Ties and Masonry Anchorage
- Furring Strips Electrical Fixtures
- Maintenance

## **FEATURES AND BENEFITS**

- + General purpose anchoring
- + Installs in a variety of base materials

## **APPROVALS AND LISTINGS**

 Federal GSA Specification Meets the proof load requirements of FF-S-325C, Group V, Type 2, Class 3, (superseded) and CID A-A 1925A, Type 1 (mushroom head) & Type 2 (flat head)

#### **GUIDE SPECIFICATIONS**

CSI Divisions: 03 16 00 - Concrete Anchors, 04 05 19.16 - Masonry Anchors, and 05 05 19 - Post-Installed Concrete Anchors, Anchors shall be Zamac Nailin anchors as supplied by DEWALT. Towson, MD.

## INSTALLATION AND MATERIAL SPECIFICATIONS

#### **Installation Specifications**

	Anchor Diameter, d						
Dimension	3/16" MH	1/4" MH	1/4" FH				
ANSI Drill Bit Size (in.)	3/16	1/4"	1/4"				
Fixture Clearance Hole (in.)	1/4	5/16	5/16				
Head Height (in.)	7/64	9/64	3/16				
Head Width (in.)	13/32	35/64	35/64				
MH = Mushroom Head FH = Flat Head							

#### **Installation Guidelines**

Using the proper diameter bit, drill a hole into the base material to a depth of at least 1/4" deeper than the required embedment. The tolerances of the drill bit used should meet the requirements of ANSI Standard B212.15. Remove dust and debris from the hole during drilling (e.g. dust extractor) or following drilling (e.g. suction, forced air) to extract loose particles created by drilling.

|--|

Insert the anchor through the fixture and into the drilled hole. Drive the nail into the anchor body to expand it. Be sure the head is seated firmly against the fixture and that the anchor is at the proper embedment. Take care not to overdrive the nail. This anchor is not recommended for installations at an angle or for use overhead.



#### SECTION CONTENTS

General Information	.1
Installation and Material Specifications	.1
Performance Data	
Design Criteria	.3
Ordering Information	.3



ZAMAC NAILIN

## ANCHOR MATERIALS

Zamac Alloy body with Carbon or Stainless Steel Drive Nail

## ANCHOR SIZE RANGE (TYP.)

• 3/16" diameter x 7/8" length to 1/4" diameter x 3" diameter

## SUITABLE BASE MATERIALS

- Normal-Weight Concrete
- Concrete Masonry (CMU)
- Brick Masonry
- Stone

# **Material Specifications**

	Component Material						
Anchor Component	Mushroom Head CS Nail	Flat Head CS Nail	Mushroom Head SS Nail				
Drive Nail	AISI 1018	AISI 1018	Type 304 SS				
Anchor Body	Zamac Alloy	Zamac Alloy	Zamac Alloy				
Nail Plating	ASTM B 633, SC	N/A					
CS = Carbon Steel SS = Stainless Steel							



Technical Guide – Mechanical Anchors ©2018 Dewalt – Rev. A

## **PERFORMANCE DATA**

## Ultimate and Allowable Load Capacities for Zamac Nailin in Normal-Weight Concrete<sup>1,2,3,4,5</sup>

		Minimum Concrete Compressive Strength, f 'c											
Nominal Anchor	Min. Embed.		2,00	0 psi			4,000 psi				6,000 psi		
Diameter	Depth	Ten	sion	Sh	ear	Ten	sion	Sh	ear	Ten	sion	Sh	ear
a in.	in. (mm)	Ultimate Ibs. (kN)	Allowable Ibs. (kN)	Ultimate Ibs. (kN)	Allowable Ibs. (kN)	Ultimate Ibs. (kN)	Allowable Ibs. (kN)	Ultimate Ibs. (kN)	Allowable Ibs. (kN)	Ultimate Ibs. (kN)	Allowable lbs. (kN)	Ultimate Ibs. (kN)	Allowable Ibs. (kN)
3/16	3/4	285	70	415	105	400	100	560	140	480	120	560	140
	(19)	(1.3)	(0.3)	(1.8)	(0.5)	(1.8)	(0.4)	(2.5)	(0.6)	(2.1)	(0.5)	(2.5)	(0.6)
	5/8	410	105	440	110	580	145	655	165	580	145	655	165
	(16)	(1.8)	(0.5)	(2.0)	(0.5)	(2.6)	(0.6)	(2.9)	(0.7)	(2.6)	(0.6)	(2.9)	(0.7)
1/4	3/4	540	135	600	150	765	190	850	215	800	200	850	215
	(19)	(2.4)	(0.6)	(2.7)	(0.7)	(3.4)	(0.8)	(3.8)	(1.0)	(3.6)	(0.9)	(3.8)	(1.0)
1/4	1	620	155	640	160	875	220	890	225	895	225	890	225
	(25)	(2.8)	(0.7)	(2.8)	(0.7)	(3.9)	(1.0)	(4.0)	(1.0)	(4.0)	(1.0)	(4.0)	(1.0)
	1-1/4	700	175	720	180	990	250	970	245	990	250	990	250
	(32)	(3.1)	(0.8)	(3.2)	(0.8)	(4.4)	(1.1)	(4.3)	(1.1)	(4.4)	(1.1)	(4.4)	(1.1)

1. Tabulated load values are for anchors installed in concrete. Concrete compressive strength must be at the specified minimum at the time of installation.

2. Allowable load capacities listed are calculated using and applied safety factor of 4.0. Anchors are not recommended for use overhead or for life safety. Consideration of safety factors of 20 or higher may be necessary depending upon the application such as in sustained tensile loading applications.

3. Linear interpolation may be used to determine allowable loads for anchors at intermediate embedment depths and compressive strengths.

4. The tabulated load values are applicable to single anchors installed at critical edge and spacing distances. Allowable load capacities are multiplied by reduction factors when anchor spacing or edge distances are less than critical distances.

5. Anchors installed flush with face or end of concrete surface.

## Ultimate and Allowable Load Capacities for Zamac Nailin in Hollow Concrete Masonry<sup>1,2,3</sup>

Nominal		f'm ≥ 1,500 psi (10.4 MPa)						
Anchor Diameter	Minimum Embedment Depth	Ultimat	te Load	Allowable Load				
d in.	in. (mm)	Tension Ibs. (kN)	Shear Ibs. (kN)	Tension Ibs. (kN)	Shear Ibs. (kN)			
3/16	3/4 (19.1)	270 (1.2)	560 (2.5)	55 (0.2)	110 (0.5)			
	5/8 (15.9) 3/4	360 (1.6) 735	655 (2.9) 850	70 (0.3) 145	130 (0.6) 170			
1/4	(19.1) 1 (25.4) 1-1/4	(3.3) 835 (3.8) 990	(3.8) 890 (4.0) 970	(0.7) 165 (0.7) 200	(0.8) 180 (0.8) 195			
	(31.7)	(4.4)	(4.3)	(0.9)	(0.9)			

1. Tabulated load values are for anchors installed in minimum 6-inch wide, minimum Grade N, Type II, lightweight, medium-weight or normal-weight concrete masonry units conforming to ASTM C 90. Mortar must be minimum Type N. Masonry compressive strength must be at the specified minimum at the time of installation (f<sup>+</sup>m ≥ 1,500 psi). Hollow masonry cells may also be grouted or solid.

2. Allowable load capacities listed are calculated using and applied safety factor of 5.0. Anchors are not recommended for use overhead or for life safety. Consideration of safety factors of 20 or higher may be necessary depending upon the application such as in sustained tensile loading applications.

3. Anchors installed flush with face or end of masonry surface.

## Ultimate and Allowable Load Capacities for Zamac Nailin in Solid or Hollow Clay Brick Masonry<sup>1,2,3</sup>

Nominal		f´m ≥ 1,500 psi (10.4 MPa)						
Anchor	Minimum Embedment Depth	Ultima	te Load	Allowab	le Load			
Diameter d in.	in. (mm)	Tension Ibs. (kN)	Shear Ibs. (kN)	Tension Ibs. (kN)	Shear Ibs. (kN)			
3/16	3/4 (19.1)	460 (2.1)	550 (2.5)	90 (0.4)	110 (0.5)			
	5/8 (15.9)	570 (2.6)	750 (3.3)	115 (0.5)	150 (0.7)			
1/4	3/4 (19.1)	790 (3.6)	840 (3.7)	160 (0.7)	170 (0.8)			
1/4	1 (25.4)	820 (3.7)	840 (3.7)	165 (0.7)	170 (0.8)			
	1-1/4 (31.7)	865 (3.9)	840 (3.7)	175 (0.8)	170 (0.8)			

1. Tabulated load values are for anchors installed in multiple wythe, minimum Grade SW, solid clay brick masonry walls conforming to ASTM C 62. Mortar must be minimum Type N. Masonry compressive strength must be at the specified minimum at the time of installation (f'm ≥ 1,500 psi).

2. Allowable load capacities listed are calculated using and applied safety factor of 5.0. Anchors are not recommended for use overhead or for life safety. Consideration of safety factors of 20 or higher may be necessary depending upon the application such as in sustained tensile loading applications.

3. Anchors installed flush with face or end of masonry surface.

REV. A

TECHNICAL GUIDE - MECHANICAL ANCHORS ©2018 DEWALT



## **DESIGN CRITERIA**

## **Combined Loading**

For anchors loaded in both shear and tension, the combination of loads should be proportioned as follows:

Where:

 $\left(\frac{\mathbf{N}\mathbf{u}}{\mathbf{N}\mathbf{n}}\right) + \left(\frac{\mathbf{V}\mathbf{u}}{\mathbf{V}\mathbf{n}}\right)$ 

≤ **1** 

 $N_n =$  Allowable Tension Load

 $N_u$  = Applied Service Tension Load  $V_u$  = Applied Service Shear Load Vn = Allowable Shear Load

## Load Adjustment Factors for Spacing and Edge Distances in Normal-Weight Concrete

Anchor Dimension	Load Type	Critical Distance (Full Anchor Capacity)	Critical Load Factor	Minimum Distance (Reduced Capacity)	Minimum Load Factor			
Spacing (s)	Tension and Shear	s <sub>cr</sub> = 10d	$F_{\text{NS}} = F_{\text{VS}} = 1.0$	$s_{min} = 5d$	$F_{\text{NS}}=F_{\text{VS}}=0.50$			
Edge Distago (0)	Tension	$c_{cr} = 12d$	$F_{NC} = 1.0$	$c_{min} = 6d$	$F_{\text{NC}} = 0.80$			
Edge Distnace (c)	Shear	c <sub>cr</sub> = 12d	$F_{VC} = 1.0$	$c_{min} = 6d$	$F_{VC} = 0.50$			
1 Allowable load values found in the performance data tables are multiplied by reduction factors when anchor spacing or edge distances are less than critical distances. Linear intermolation is								

allowed for intermediate anchor spacing and edge distances between critical and minimum distances. When an anchor is affected by both reduced spacing and edge distance, the spacing and edge reduction factors must be combined (multiplied). Multiple reduction factors for anchor spacing and edge distance may be required depending on the anchor group configuration.

## **ORDERING INFORMATION**

## **Mushroom Head Zamac Nailin with Carbon Steel Nail**

Catalog Number	Anchor Size	Drill Diameter	Standard Box	Standard Carton	Wt./ 100		
2802	3/16" x 7/8"	3/16"	100	500	3/4		
2806	1/4" x 3/4"	1/4"	100	500	1-1/2		
2808	1/4" x 1"	1/4"	100	500	1-3/4		
2814	1/4" x 1-1/4"	1/4"	100	500	2-1/4		
2820	1/4" x 1-1/2"	1/4"	100	500	2-1/2		
2826	1/4" x 2"	1/4"	100	500	3		
2804	1/4" x 3"	1/4"	100	500	4		
The published size includes the diameter and length of the anchor measured from under the shoulder of the anchor body.							



# Master Pack Mushroom Head Zamac Nailin with Carbon Steel Nail

Catalog Number	Anchor Size	Drill Diameter	Standard Box	Standard Carton	Wt./ 100			
2803	3/16" x 7/8"	3/16"	-	1,000	3/4			
2807	1/4" x 3/4"	1/4"	-	1,000	1-1/2			
2809	1/4" x 1"	1/4"	-	1,000	1-3/4			
2815	1/4" x 1-1/4"	1/4"	-	1,000	2-1/4			
2821	1/4" x 1-1/2"	1/4"	-	1,000	2-1/2			
2827	1/4" x 2"	1/4"	-	1,000	3			
2805	1/4" x 3"	1/4"	-	1,000	4			
The published size incl	The published size includes the diameter and length of the anchor measured from under the shoulder of the anchor body.							

## Flat Head Zamac Nailin with Carbon Steel Nailin

Catalog Number	Anchor Size	Drill Diameter	Standard Box	Standard Carton	Wt./ 100		
2836	1/4" x 1-1/2"	1/4"	100	500	2-1/2		
2838 1/4" x 2" 1/4" 100 500 3							
The published size includes the diameter and length of the anchor measured from under the shoulder of the anchor body.							

## **Mushroom Head Zamac Nailin with Stainless Steel Nailin**

Catalog Number	Anchor Size	Drill Diameter	Standard Box	Standard Carton	Wt./ 100	
2858	1/4" x 1"	1/4"	100	500	1-3/4	
2864	1/4" x 1-1/4"	1/4"	100	500	2-1/4	
2870	1/4' x 1-1/2"	1/4"	100	500	2-1/2	
2876	1/4" x 2"	1/4"	100	500	3	
The published size includes the diameter and length of the anchor measured from under the shoulder of the anchor body.						



